



# TL Mini Standard Colours

## TL Mini 13W/54-765 1FM/10X25CC

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

### Product data

General Information	
Cap-Base	G5 [ G5]
Life To 10% Failures (Nom)	4000 h
Life to 50% Failures (Nom)	8000 h
Life to 50% Failures Preheat (Nom)	8000 h
System Description	na [ -]

Light Technical	
Colour Code	54-765
Luminous Flux (Nom)	740 lm
Colour Designation	Cool Daylight
Lumen Maintenance 10000 h (Nom)	58 %
Lumen Maintenance 2000 h (Nom)	85 %
Lumen Maintenance 5000 h (Nom)	70 %
Colour Temperature, horizontal (Nom)	6200 K
Luminous Efficacy (rated) (Nom)	57 lm/W
Colour Rendering Index horiz (Nom)	75

Operating and Electrical	
Power (Rated) (Nom)	13.0 W
Lamp Current (Nom)	0.170 A
Voltage (Nom)	90 V

Controls and Dimming	
Dimmable	Yes

Approval and Application	
Energy Efficiency Label	A
Mercury (Hg) Content (Nom)	4.4 mg
Energy Consumption kWh/1000 h	14 kWh


Product Data	
Full product code	871150071671227
Order product name	TL Mini 13W/54-765 FAM/10X25BOX
EAN/UPC - Product	8711500716712
Order code	71671227
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	250
Material Nr. (12NC)	928001505440
Net Weight (Piece)	50.340 g
ILCOS Code	FD-13/62/2A-E-G5

## TL Mini Standard Colours

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


### Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL Mini 13W/54-765 FAM/10X25BOX	16 mm	516.9 mm	524.0 mm	521.6 mm	531.1 mm

### TL Mini 13W/54-765

### Photometric data



### Lightcolour /54-765



### Lightcolour /54-765

