



MASTER TL Mini Super 80

MASTER TL Mini Super 80 13W/840 1FM/10X25CC

This TL Miniature lamp (tube diameter 16 mm) is a lamp with small dimensions, which enables system miniaturization and offers the possibility of operation on low-voltage DC supply. It is ideal for applications where better color rendering and efficacy (than standard colors) are required and where space is limited, e.g. halls, staircase lighting in apartment buildings, built into furniture, mirror and cupboard lighting, signage and emergency lighting.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Operating and Electrical	
Cap base	G5 [G5]	Chromaticity coordinate X (nom.)	0.38
Life to 10% failures (nom.)	4000 h	Chromaticity coordinate Y (nom.)	0.38
Life to 50% failures (nom.)	8000 h	Correlated Colour Temperature (Nom)	4000 K
Life to 50% failures preheat (nom.)	8000 h	Luminous efficacy (rated) (nom.)	77 lm/W
	Sphere	Colour rendering index (nom.)	82
Light Technical		Controls and Dimming	
Colour Code	841 [CCT of 4100K (841)]	Dimmable	Yes
Luminous flux (nom.)	1000 lm		
Colour designation	Cool White (CW)		
Lumen maintenance 10,000 hours (nom.)	71 %		
Lumen maintenance 2,000 hours (nom.)	90 %		
Lumen maintenance 5,000 hours (nom.)	77 %		

MASTER TL Mini Super 80

Mechanical and Housing

Bulb shape T5 [16 mm (T5)]

Approval and Application


Energy Efficiency Class G
 Mercury (Hg) content (max.) 2.5 mg
 Mercury (Hg) content (nom.) 3.0 mg
 Energy consumption kWh/1,000 hours 14 kWh
 423503

Product Data

Full product code 871150071685927

Order product name	MASTER TL Mini Super 80 13W/840 FAM/10X25BOX
EAN/UPC – product	8711500716859
Order code	71685927
SAP numerator – quantity per pack	1
Numerator – packs per outer box	250
SAP material	928001508450
SAP net weight (piece)	40.200 g
ILCOS code	FD-13/40/1B-E-G5


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL Mini Super 80 13W/840 FAM/10X25BOX	16 mm	516.9 mm	524.0 mm	521.6 mm	531.1 mm

TL 13W/840

Photometric data



LDPB_TL8MINI_840-Spectral power distribution B/W



Lightcolour /840

MASTER TL Mini Super 80

