



T12 Standard

F20T12/D-765 25 PK

Low-pressure mercury discharge lamps with a tubular 37 mm envelope


Product data

| General Information | |
|------------------------------------|---------------------------------|
| Cap-Base | G13 [Medium Bi-Pin Fluorescent] |
| Life to 50% Failures (Nom) | 9,000 hour(s) |
| Light Technical | |
| Color Code | 54-765 |
| Luminous Flux | 975 lm |
| Color Designation | Cool Daylight |
| Correlated Color Temperature (Nom) | 6200 K |
| Color rendering index (CRI) | 72 |
| Operating and Electrical | |
| Power Consumption | 19.3 W |
| Voltage (Nom) | 59 V |
| Voltage (Nom) | 59 V |
| Controls and Dimming | |
| Dimmable | Yes |

| Mechanical and Housing | |
|---------------------------------|--------------------|
| Bulb Shape | T12 [38 mm (T12)] |
| Approval and Application | |
| Mercury (Hg) Content (Nom) | 8.0 mg |
| Product Data | |
| Order product name | F20T12/D-765 25 PK |
| Full product name | F20T12/D-765 25 PK |
| Full product code | 871869667308900 |
| Order code | 928003505415 |
| Material Nr. (12NC) | 928003505415 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718696673089 |
| Numerator - Packs per outer box | 25 |
| EAN/UPC - Case | 8718696673096 |


T12 Standard

Dimensional drawing



| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|--------------------|---------|----------|----------|----------|---------|
| F20T12/D-765 25 PK | 40.5 mm | 589.8 mm | 596.9 mm | 594.5 mm | 604 mm |

Photometric data



Spectral Power Distribution Colour - F20T12/D-765 25 PK

