



T12 Standard

F40T12/54-765 1SL/25

Low-pressure mercury discharge lamps with a tubular 37 mm envelope


Product data

| General Information | |
|------------------------------------|---------------------------------|
| Cap-Base | G13 [Medium Bi-Pin Fluorescent] |
| Life to 50% Failures (Nom) | 13,000 hour(s) |
| Light Technical | |
| Luminous Flux | 2,500 lm |
| Color Designation | 6500 Kelvin |
| Correlated Color Temperature (Nom) | 6500 K |
| Color rendering index (CRI) | 72 |
| Operating and Electrical | |
| Power Consumption | 40 W |
| Voltage (Nom) | 107 V |
| Voltage (Nom) | 107 V |
| Mechanical and Housing | |
| Bulb Shape | T-12 (T12) |

| Approval and Application | |
|---------------------------------|----------------------|
| Mercury (Hg) Content (Nom) | 8 mg |
| Product Data | |
| Order product name | F40T12/54-765 1SL/25 |
| Full product name | F40T12/54-765 1SL/25 |
| Full product code | 871869966082600 |
| Order code | 928006005401 |
| Material Nr. (12NC) | 928006005401 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718699660826 |
| Numerator - Packs per outer box | 25 |
| EAN/UPC - Case | 8718699660833 |

T12 Standard

Dimensional drawing



| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|----------------------|---------|------------|------------|------------|------------|
| F40T12/54-765 1SL/25 | 40.5 mm | 1,199.4 mm | 1,206.5 mm | 1,204.1 mm | 1,213.6 mm |

