



Flexo Print

TL 60W/10-R SLV/25

Flexo print TL lamps emit almost all of their light (99.9%) in the useful UVA and visible blue wavebands – between 350 and 400 nm – and have peak intensity at 370 nm (except for the /03 version). This makes them ideal for flexo printing equipment and photopolymerization processes. In addition, the ‘R’ lamps in the family have an internal 200-degree reflector to further optimize the lamp’s overall efficiency.

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	G13 [Medium Bi-Pin Fluorescent]
壽命 (故障率 50%) (標稱)	2,000 h
可用使用始間 (標稱)	1,000 h
照明技術	
色碼	10-R
色彩名稱	紫外線 A
色度坐標 X (標稱)	222
色度坐標 Y (Nom)	210
1000 小時後的 UV 衰減	15 %
2000 小時後的 UV 衰減	30 %
500 小時後的 UV 衰減	10 %
運轉與電力	
耗電量	62 W


燈具電流 (標稱)	0.7 A
電壓 (標稱)	102 V
電壓 (標稱)	102 V
機械與外罩	
燈泡形狀	T38 [T 38mm]
認證與應用	
汞 (Hg) 含量 (標稱)	13.0 mg
UV	
UV-A 輻射 100Hr (IEC)	15.8 W
產品資料	
下訂產品名稱	TL 60W/10-R SLV/25
完整產品名稱	TL 60W/10-R SLV/25

完整產品代碼	871150061572540
訂單代碼	928008401003
材質 Nr. (12NC)	928008401003
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500615725


分子 - 每一外盒包裝	25
EAN/UPC - 箱	8711500615732

二维绘图

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 60W/10-R SLV/25	40.5 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm



光度数据



Spectral Power Distribution Colour - TL 60W/10-R SLV/25

