

PHILIPS

Lighting



Actinic BL TL(-K)/TL-D(-K)

Actinic BL TL 40W/10 SLV/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

Product data


General Information		Voltage (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		101 V
Main Application	Insect traps	Approval and Application	
Life to 50% Failures (Nom)	9000 h	Mercury (Hg) Content (Nom)	13.0 mg
Useful Life (Nom)	5000 h	UV	
System Description	RS [Rapid Start (RS)]	UV-B/UV-A (IEC)	0.2 %
Light Technical		UV-A Radiation 100Hr (IEC)	10.0 W
Color Code	10	UV-A Radiation 0Hr (IEC)	12.4 W
Color Designation	Actinic	Product Data	
Chromaticity Coordinate X (Nom)	222	Order product name	Actinic BL TL 40W/10 SLV/25
Chromaticity Coordinate Y (Nom)	210	EAN/UPC - Product	8711500260260
UV Depreciation at 2000 h	20 %	Order code	391532
UV Depreciation at 5000 h	40 %	Numerator - Quantity Per Pack	1
Operating and Electrical		Numerator - Packs per outer box	25
Power (Rated) (Nom)	39 W	Material Nr. (12NC)	928011301020
Lamp Current (Nom)	0.43 A	Net Weight (Piece)	292.000 g

Actinic BL TL(-K)/TL-D(-K)

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL 40W/10 SLV/25	40.5 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm

TL 40W/10 RS

Photometric data



Lightcolor /10



Lightcolor /10

