



# TL Rapid Start Standard Colours

## TL RS 40W/54-765 1SL/25


The TL RS (Rapid Start) lamp (tube diameter 38 mm) has an external silicon coating. It is suitable for situations where high humidity requires fast and stable ignition but color rendering is not important. Rapid Start lamps can be ignited without a starter.

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	54-765
Luminous Flux	2,500 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6200 K
Luminous Efficacy (rated) (Nom)	64 lm/W
Color rendering index (CRI)	72
Operating and Electrical	
Power Consumption	39.0 W
Lamp Current (Nom)	0.430 A
Voltage (Nom)	101 V
Voltage (Nom)	101 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T12
Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg
Product Data	
Order product name	TL RS 40W/54-765 1SL/25
Full product name	TL RS 40W/54-765 1SL/25
Full product code	871150064133500
Order code	928011305430
Material Nr. (12NC)	928011305430
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500641335
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500641342


# TL Rapid Start Standard Colours

## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL RS 40W/54-765 1SL/25	40.5 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

## Photometric data



Spectral Power Distribution Colour - TL RS 40W/54-765 1SL/25

