



TL Blacklight Blue

F40T12/BLACKLIGHT/48 BLB LF

TL/08 Blacklight Blue lamps are low-pressure mercury-vapor fluorescent lamps. They have an inner envelope coated with a fluorescent powder that emits long-wave UV radiation to excite luminescence.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Main Application	Blacklight Blue
Life to 50% Failures (Nom)	9000 h
Useful Life (Nom)	5000 h
System Description	Rapid Start (RS)

Light Technical	
Color Code	108 [08 lead free glass]
Color Designation	Blacklight Blue
LLMF 2000 h Rated	5 %
LLMF 6000 h Rated	10 %

Operating and Electrical	
Power (Rated) (Nom)	39 W
Lamp Current (Nom)	0.43 A
Voltage (Nom)	104 V

Approval and Application	
Mercury (Hg) Content (Nom)	13.0 mg

UV	
UV-B/UV-A (IEC)	0.2 %
UV-A Radiation 100Hr (IEC)	9.6 W
UV-A Radiation 0Hr (IEC)	9.8 W


Product Data	
Order product name	F40T12/BLACKLIGHT/48 BLB LF
EAN/UPC - Product	046677157623
Order code	157628
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	928011310821
Net Weight (Piece)	0.310 kg

Warnings and Safety

- Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

TL Blacklight Blue



Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
F40T12/BLACKLIGHT/48	40.5 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm
BLB LF					

TL 40W/108 RS

Photometric data



TL Blacklight Blue /08

TL Blacklight Blue /08

