



Actinic BL TL(-K) / TL-D(-K)

Actinic BL TL-DK 36W/10 1SL/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	9,000 hour(s)
Useful Life (Nom)	5,000 hour(s)
Light Technical	
Color Code	10
Color Designation	Actinic
Chromaticity Coordinate X (Nom)	225


Chromaticity Coordinate Y (Nom)	230
Operating and Electrical	
Power Consumption	36 W
Lamp Current (Nom)	0.865 A
Voltage (Nom)	50 V
Voltage (Nom)	50 V

Actinic BL TL(-K) / TL-D(-K)

Mechanical and Housing	
Bulb Shape	T26
Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg
UV	
UV-A Radiation 100Hr (IEC)	8.8 W
Product Data	
Order product name	Actinic BL TL-DK 36W/10 1SL/25


Full product name	Actinic BL TL-DK 36W/10 1SL/25
Full product code	872790086083200
Order code	286724
Material Nr. (12NC)	928019701003
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900860832
Numerator - Packs per outer box	25
EAN/UPC - Case	8727900860849

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-DK 36W/10 1SL/25	1-1/8 inch	23-1/4 inch	23-1/2 inch	23-7/16 inch	23-13/16 inch

Photometric data



Spectral Power Distribution Colour - Actinic BL TL-DK 36W/10 1SL/25

Actinic BL TL(-K) / TL-D(-K)

