



# Retail Sales T8

## F15T8/COOL WHITE PLUS/18 ALTO 6PK

Energy Savings, extra long life, extra low mercury T8 lamps offer high energy savings, superior lumen output, and long life in an environmentally responsible lamp.

### Product data

General Information	
Base	G13 [ Medium Bi-Pin Fluorescent]
Life To 10% Failures (Nom)	10000 h
Life to 50% Failures (Nom)	13000 h
Features	ALTO® (ALTO)

Light Technical	
Color Code	33-640
Initial lumen (Nom)	830 lm
Color Designation	Cool White (CW)
Lumen Maintenance 10000 h (Nom)	75 %
Lumen Maintenance 2000 h (Nom)	90 %
Lumen Maintenance 5000 h (Nom)	80 %
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	63

Operating and Electrical	
Power (Rated) (Nom)	15.5 W
Lamp Current (Nom)	0.335 A
Voltage (Nom)	55 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Cap-Base Information	Green [ Green Cap]

Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg


Product Data	
Order product name	F15T8/COOL WHITE PLUS/18 ALTO SL 6
EAN/UPC - Product	046677392079
Order code	392076
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	928022803328
Net Weight (Piece)	59.600 g

### Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

# Retail Sales T8


## Dimensional drawing




TL-D F15T8 Cool White/GC ALTO

Product	D (max)	A (max)	B (max)	B (min)	C (max)
F15T8/COOL WHITE	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm
PLUS/18 ALTO SL 6					

## Photometric data




Lightcolor /33-640




Lightcolor /33-640

## Lifetime




TL-D Standard Colours Life Expectancy 3 h cycle



TL-D Standard Colours Life Expectancy 12 h cycle

## Retail Sales T8

### Lifetime



TL-D Standard Colours Lumen Maintenance 3 h + 12 h cycle

