



# Preheat T8

## F15T8/D 25PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

### Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050


### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	54-765
Luminous Flux	725 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6200 K
Color rendering index (CRI)	75
Operating and Electrical	
Power Consumption	15 W
Lamp Current (Nom)	0.335 A
Wattage Equivalent	15 W
Voltage (Nom)	55 V
Voltage (Nom)	55 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg
Product Data	
Order product name	F15T8/D 25PK
Full product name	F15T8/D 25PK
Order code	407205
Material Nr. (12NC)	928022805425
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677378233
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677407204


Preheat T8

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
F15T8/D 25PK	1-1/8 inch	17-1/4 inch	17-1/2 inch	17-7/16 inch	17-13/16 inch

Photometric data




Spectral Power Distribution Colour - F15T8/D 25PK

Lifetime




Life Expectancy Diagram - F15T8/D 25PK



Life Expectancy Diagram - F15T8/D 25PK

Preheat T8

Lifetime



Lumen Maintenance Diagram - F15T8/D 25PK

