



Retail Sales T8

F15T8 BRIGHT WHITE/18 ALTO 6PK

Energy Savings, extra long life, extra low mercury T8 lamps offer high energy savings, superior lumen output, and long life in an environmentally responsible lamp.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General information	
Base	G13 [Medium Bi-Pin Fluorescent]
Life To 10% Failures (Nom)	10000 h
Life to 50% Failures (Nom)	13000 h
Features	ALTO® (ALTO)

Light technical	
Color Code	830 [CCT of 3000K]
Initial lumen (Nom)	990 lm
Color Designation	Soft White
Lumen Maintenance 2000 h (Nom)	93 %
Lumen Maintenance 5000 h (Nom)	88 %
Correlated Color Temperature (Nom)	3000 K
Color Rendering Index (Nom)	83

Operating and electrical	
Power (Rated) (Nom)	15.5 W
Lamp Current (Nom)	0.335 A
Voltage (Nom)	55 V

Controls and dimming	
Dimmable	Yes

Mechanical and housing	
Cap-Base Information	Green [Green Cap]
Bulb Shape	T8 [26 mm (T8)]

Approval and application	
Mercury (Hg) Content (Nom)	2.0 mg

Product data	
Order product name	F15T8 BRIGHT WHITE/18 ALTO SL6
EAN/UPC - Product	046677392123
Order code	392126
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	928022883028
Net Weight (Piece)	59.600 g

Retail Sales T8


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
F15T8 BRIGHT WHITE/18	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm
ALTO SL6					

F15T8 BRIGHT WHITE/18 ALTO SL6


Lifetime



LDLE_TL-DSTD_0001-Life expectancy diagram



LDLE_TL-DSTD_0002-Life expectancy diagram



LDLM_TL-DSTD_0001-Lumen maintenance diagram

