



# Retail Sales T8

## F15T8 BRIGHT WHITE/18 ALTO 6PK

Energy Savings, extra long life, extra low mercury T8 lamps offer high energy savings, superior lumen output, and long life in an environmentally responsible lamp.

### Product data

| General Information        |                                  |
|----------------------------|----------------------------------|
| Base                       | G13 [ Medium Bi-Pin Fluorescent] |
| Life To 10% Failures (Nom) | 10000 h                          |
| Life to 50% Failures (Nom) | 13000 h                          |
| Features                   | ALTO® (ALTO)                     |

| Light Technical                    |                     |
|------------------------------------|---------------------|
| Color Code                         | 830 [ CCT of 3000K] |
| Initial lumen (Nom)                | 990 lm              |
| Color Designation                  | Soft White          |
| Lumen Maintenance 2000 h (Nom)     | 93 %                |
| Lumen Maintenance 5000 h (Nom)     | 88 %                |
| Correlated Color Temperature (Nom) | 3000 K              |
| Color Rendering Index (Nom)        | 83                  |

| Operating and Electrical |         |
|--------------------------|---------|
| Power (Rated) (Nom)      | 15.5 W  |
| Lamp Current (Nom)       | 0.335 A |
| Voltage (Nom)            | 55 V    |

| Controls and Dimming |     |
|----------------------|-----|
| Dimmable             | Yes |

| Mechanical and Housing |                    |
|------------------------|--------------------|
| Cap-Base Information   | Green [ Green Cap] |

| Approval and Application      |        |
|-------------------------------|--------|
| Energy Efficiency Label (EEL) | A      |
| Mercury (Hg) Content (Nom)    | 2.0 mg |

| Product Data                    |                                |
|---------------------------------|--------------------------------|
| Order product name              | F15T8 BRIGHT WHITE/18 ALTO SL6 |
| EAN/UPC - Product               | 046677392123                   |
| Order code                      | 392126                         |
| Numerator - Quantity Per Pack   | 1                              |
| Numerator - Packs per outer box | 6                              |
| Material Nr. (12NC)             | 928022883028                   |
| Net Weight (Piece)              | 59.600 g                       |

### Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

# Retail Sales T8


## Dimensional drawing




| Product             | D (max) | A (max)  | B (max)  | B (min)  | C (max)  |
|---------------------|---------|----------|----------|----------|----------|
| F15T8 SOFT WHITE/18 | 28 mm   | 437.4 mm | 444.5 mm | 442.1 mm | 451.6 mm |
| ALTO SL6            |         |          |          |          |          |

TL-D F15T8 Soft White/GC ALTO


## Lifetime



TL-D Standard Colours Life Expectancy 3 h cycle



TL-D Standard Colours Life Expectancy 12 h cycle



TL-D Standard Colours Lumen Maintenance 3 h + 12 h cycle

