



TL-D Standard Colours

TL-D 10W/54-765 1SL/50

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	5,000 hour(s)
Light Technical	
Color Code	54-765
Luminous Flux	390 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6200 K
Color rendering index (CRI)	75
Operating and Electrical	
Power Consumption	10.0 W
Lamp Current (Nom)	0.230 A
Voltage (Nom)	46 V


Voltage (Nom)	46 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg
Product Data	
Order product name	TL-D 10W/54-765 1SL/50
Full product name	TL-D 10W/54-765 1SL/50
Full product code	871150064130465
Order code	928024005436

TL-D Standard Colours

Material Nr. (12NC)	928024005436
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500641304
Numerator - Packs per outer box	50


EAN/UPC - Case	8711500641311
----------------	---------------

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 10W/54-765 1SL/50	28 mm	331.5 mm	338.6 mm	336.2 mm	345.7 mm

Photometric data




Spectral Power Distribution Colour - TL-D 10W/54-765 1SL/50

Lifetime



Life Expectancy Diagram - TL-D 10W/54-765 1SL/50



Life Expectancy Diagram - TL-D 10W/54-765 1SL/50

TL-D Standard Colours

Lifetime



Lumen Maintenance Diagram - TL-D 10W/54-765 1SL/50

