



Actinic BL TL(-K)/TL-D(-K)

Actinic BL TL-D 15W/10 1SL/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

产品数据

基本資訊	
接口	G13 [Medium Bi-Pin Fluorescent]
主要應用	Reprography (R)
至 50% 故障的使用時間 (標稱)	8000 h
可用使用時間 (標稱)	5000 h
照明科技	
色碼	10
色彩名稱	Actinic
色度座標 X (標稱)	222
色度座標 Y (標稱)	210
500 小時後的流明衰減	10 %
500 小時後的流明衰減	15 %
500 小時後的流明衰減	20 %
運作和電氣	
Power (Rated) (Nom)	15 W
燈具電流 (標稱)	0.34 A


電壓 (標稱)	51 V
應用	
汞 (Hg) 含量 (標稱)	5.0 mg
紫外線	
UV-B/UV-A (IEC)	0.2 %
UV-A 輻射 100Hr (IEC)	3.5 W
產品參數	
完整產品碼	871150071093240
訂購產品名稱	Actinic BL TL-D 15W/10 1SL/25
EAN/UPC - 產品	8711500710932
訂購代碼	928024801029
分子 - 各件數量	1
分子 - 每一外盒內件數	25
材質編號(12NC)	928024801029
淨重 (件)	56.570 g

Actinic BL TL(-K)/TL-D(-K)

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

二维绘图



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 15W/10 1SL/25	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm

TL-D 15W/10

光度数据

