

# PHILIPS

## Lighting



# Actinic BL TL(-K)/TL-D(-K)

## F15T8/BL 25PK

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

### Product data


General Information		Voltage (Nom)	
Base	G13 [ Medium Bi-Pin Fluorescent]		51 V
Main Application	Reprography (R)	Approval and Application	
Life to 50% Failures (Nom)	8000 h	Mercury (Hg) Content (Nom)	5.0 mg
Useful Life (Nom)	5000 h	UV	
Light Technical		UV-B/UV-A (IEC)	0.2 %
Color Code	10	UV-A Radiation 100Hr (IEC)	3.5 W
Color Designation	Actinic	Product Data	
Chromaticity Coordinate X (Nom)	222	Order product name	Actinic BL TL-D 15W/10 ISL/25
Chromaticity Coordinate Y (Nom)	210	EAN/UPC - Product	8711500710932
UV Depreciation at 2000 h	10 %	Order code	130369
UV Depreciation at 5000 h	15 %	Numerator - Quantity Per Pack	1
UV Depreciation at 8000 h	20 %	Numerator - Packs per outer box	25
Operating and Electrical		Material Nr. (12NC)	928024801029
Power (Rated) (Nom)	15 W	Net Weight (Piece)	56.570 g
Lamp Current (Nom)	0.34 A		

# Actinic BL TL(-K)/TL-D(-K)

## Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050



## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 15W/10 1SL/25	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm

### TL-D 15W/10

## Photometric data



### Lightcolor /10

### Lightcolor /10

