



TL-D Blacklight Blue

TL-D 15W BLB 1SL/25

TL-D/08 Blacklight Blue lamps are low-pressure mercury-vapor fluorescent lamps. They have an inner envelope coated with a fluorescent powder that emits long-wave UV radiation to excite luminescence.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information		Mechanical and Housing	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Bulb Shape	T26 [T 26mm]
Life to 50% Failures (Nom)	8,000 hour(s)	Approval and Application	
Useful Life (Nom)	5,000 hour(s)	Mercury (Hg) Content (Nom)	5.0 mg
Light Technical		UV	
Color Code	108 [08 lead free glass]	UV-A Radiation 100Hr (IEC)	3.0 W
Color Designation	Blacklight Blue	Product Data	
Operating and Electrical		Order product name	TL-D 15W BLB 1SL/25
Power Consumption	15.9 W	Full product name	TL-D 15W BLB 1SL/25
Lamp Current (Nom)	0.310 A	Full product code	871150095109040
Voltage (Nom)	54 V	Order code	928024810803
Voltage (Nom)	54 V	Material Nr. (12NC)	928024810803
		Numerator - Quantity Per Pack	1

TL-D Blacklight Blue


EAN/UPC - Product/Case	8711500951090
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500951106

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 15W BLB 1SL/25	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm

Photometric data



Spectral Power Distribution Colour - TL-D 15W BLB 1SL/25

