



# TL-D Standard Colours

## TL-D 30W/54-765 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

### Product data

General Information	
Cap base	G13 [ Medium Bi-Pin Fluorescent]
Life to 10% failures (nom.)	10000 h
Life to 50% failures (nom.)	13000 h
Light Technical	
Colour Code	54-765
Lamp Luminous Flux 25°C EL (Nom)	1825 lm
Colour Designation	Cool Daylight
Lumen maintenance 10,000 hours (nom.)	75 %
Lumen maintenance 2,000 hours (nom.)	90 %
Lumen maintenance 5,000 hours (nom.)	80 %
Colour Temperature, horizontal (Nom)	6200 K
Colour Rendering Index, horiz (Nom)	72
Operating and Electrical	
Power (Rated) (Nom)	30.0 W
Lamp current (nom.)	0.360 A
Voltage (Nom)	98 V


Controls and Dimming	
Dimmable	yes
Approval and Application	
Energy efficiency label (EEL)	B
Mercury (Hg) content (nom.)	8.0 mg
Energy Consumption kWh/1000 h	36 kWh
Product Data	
Full product code	871150072263800
Order product name	TL-D 30W/54-765 1SL/25
EAN/UPC – product	8711500722638
Order code	928025405482
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	928025405482
Net weight (piece)	0.130 kg
ILCOS Code	FD-30/62/2A-E-G13

## TL-D Standard Colours

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


### Dimensional drawing




TL-D 30W/54-765

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 30W/54-765 1SL/25	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8 mm

### Photometric data





Lightcolour /54-765



Lightcolour /54-765

### Lifetime



## TL-D Standard Colours

### Lifetime

