



# TL-E 80

## TL-E 22W/865 1CT/20

Fluorescent lamps with a circular tube having a diameter of 26 mm


### Product data

General Information	
Cap base	G10Q [ G10q]
Life to 50% failures (nom.)	13000 h
LSF 2000 h Rated	98 %
LSF 4000 h Rated	77 %
LSF 6000 h Rated	60 %
LSF 8000 h Rated	45 %
Light Technical	
Colour Code	865 [ CCT of 6,500 K]
Lamp Luminous Flux 25°C EL (Nom)	1250 lm
Lamp Luminous Flux (Nom)	1250 lm
Colour Designation	Cool Daylight
Colour Temperature, horizontal (Nom)	6500 K
Lamp Luminous Efficacy EM (Nom)	57 lm/W
Colour Rendering Index,horiz (Nom)	80
LLMF 2000 h Rated	80 %
LLMF 4000 h Rated	74 %
LLMF 6000 h Rated	70 %
LLMF 8000 h Rated	67 %
Operating and Electrical	
Power (Rated) (Nom)	22.0 W
Lamp current (nom.)	0.400 A
Voltage (Nom)	62 V

Temperature	
Design temperature (nom.)	25 °C
Controls and Dimming	
Dimmable	yes
Approval and Application	
Energy efficiency label (EEL)	B
Mercury (Hg) content (nom.)	8 mg
Energy Consumption kWh/1000 h	24 kWh
Product Data	
Full product code	871150028667300
Order product name	TL-E 22W/865 1CT/20
EAN/UPC – product	8711500286673
Order code	928026286574
Numerator – quantity per pack	1
Numerator – packs per outer box	20
Material no. (12NC)	928026286574
Net weight (piece)	0.110 kg
ILCOS Code	FSC-22/65/1B-E-G10q-29/210

## TL-E 80

### Dimensional drawing



TL-E 22W/865

Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
TL-E 22W/865	30.9 mm	26.2 mm	205.0 mm	213.5 mm	149.1 mm	155.6 mm
1CT/20						

