



TL-E LIFEMAX

Standard Colours

TL-E 32W/33-640 1CT/20

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes where color rendering is not important.


Product data

General Information	
Cap-Base	G10Q [G10q]
Nominal lifetime	8,000 hour(s)
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	33-640
Luminous Flux	2,050 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	64 lm/W
Color rendering index (CRI)	63
Operating and Electrical	
Power Consumption	32.0 W
Lamp Current (Nom)	0.450 A
Voltage (Nom)	81 V
Voltage (Nom)	81 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	C-T9 [C-T9 29 mm]
Approval and Application	
Mercury (Hg) Content (Nom)	9 mg
Product Data	
Order product name	TL-E 32W/33-640 1CT/20
Full product name	TL-E 32W/33-640 1CT/20
Full product code	871150055956200
Order code	928026303336
Material Nr. (12NC)	928026303336
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500559562
Numerator - Packs per outer box	20
EAN/UPC - Case	8711500559593


TL-E LIFEMAX Standard Colours

Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
TL-E 32W/33-640	30.9 mm	27.1 mm	299.0 mm	303.5 mm	241.0 mm	246.0 mm
1CT/20						

Photometric data



Spectral Power Distribution Colour - TL-E 32W/33-640 1CT/20

