



TL-E Circular Standard Colours

TL-E 32W/33-640 1CT/12

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes where color rendering is not important.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Lamp Current (Nom)	
Cap-Base	G10q		0.450 A
Life to 50% Failures (Nom)	13,000 hour(s)	Voltage (Nom)	81 V
		Voltage (Nom)	81 V
Light Technical		Controls and Dimming	
Color Code	33-640	Dimmable	Yes
Luminous Flux	2,050 lm		
Color Designation	Cool White (CW)	Mechanical and Housing	
Correlated Color Temperature (Nom)	4100 K	Bulb Shape	C-T29
Luminous Efficacy (rated) (Nom)	64 lm/W		
Color rendering index (CRI)	63	Approval and Application	
		Mercury (Hg) Content (Nom)	9 mg
Operating and Electrical			
Power Consumption	32.0 W		


TL-E Circular Standard Colours

Product Data

Order product name	TL-E 32W/33-640 1CT/12
Full product name	TL-E 32W/33-640 1CT/12
Full product code	871150055956215
Order code	928026303360
Material Nr. (12NC)	928026303360
Local order code	9280-263-03360


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500559562
Numerator - Packs per outer box	12
EAN/UPC - Case	8711500559371

Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
TL-E 32W/33-640 1CT/12	30.9 mm	27.1 mm	299.0 mm	303.5 mm	241.0 mm	246.0 mm

Photometric data



Spectral Power Distribution Colour - TL-E 32W/33-640 1CT/12

