



# MASTER TL-E Circular Super 80

## TL-E 32W/830 1CT/20

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes, including decorative ones, in 'human' applications such as schools, offices, shops and homes, and for lighting of residential areas.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


<b>General Information</b>		<b>Voltage (Nom)</b>		81 V
Cap-Base	G10Q [G10q]	<b>Voltage (Nom)</b>		81 V
Nominal lifetime	8,000 hour(s)			
Life to 50% Failures (Nom)	13,000 hour(s)			
<b>Light Technical</b>		<b>Controls and Dimming</b>		
Color Code	830 [CCT of 3000K]	Dimmable		Yes
Luminous Flux	2,375 lm	<b>Mechanical and Housing</b>		
Color Designation	Warm White (WW)	Bulb Shape		C-T9 [C-T9 29 mm]
Correlated Color Temperature (Nom)	3000 K	<b>Approval and Application</b>		
Luminous Efficacy (rated) (Nom)	74 lm/W	Mercury (Hg) Content (Nom)		8 mg
Color rendering index (CRI)	80	Energy Consumption kWh/1000 h		35 kWh
<b>Operating and Electrical</b>		<b>Product Data</b>		
Power Consumption	32.0 W	Order product name		TL-E 32W/830 1CT/20
Lamp Current (Nom)	0.450 A	Full product name		TL-E 32W/830 1CT/20

# MASTER TL-E Circular Super 80

Full product code	871150055967800
Order code	928026383074
Material Nr. (12NC)	928026383074
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500559678


Numerator - Packs per outer box	20
EAN/UPC - Case	8727900813593

## Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
TL-E 32W/830 1CT/20	30.9 mm	27.1 mm	299.0 mm	303.5 mm	241.0 mm	246.0 mm

## Photometric data



Spectral Power Distribution Colour - TL-E 32W/830 1CT/20

