



MASTER TL-E Circular Super 80

TL-E 32W/830 1CT/20

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes, including decorative ones, in 'human' applications such as schools, offices, shops and homes, and for lighting of residential areas.

Product data

General Information		LLMF 8000 h Rated	
Cap-Base	G10Q [G10q]		73 %
Life to 50% Failures (Nom)	13000 h	Operating and Electrical	
LSF 2000 h Rated	98 %	Power (Rated) (Nom)	32.0 W
LSF 4000 h Rated	77 %	Lamp Current (Nom)	0.450 A
LSF 6000 h Rated	60 %	Voltage (Nom)	81 V
LSF 8000 h Rated	45 %	Temperature	
Light Technical		Design Temperature (Nom)	25 °C
Color Code	830 [CCT of 3000K]	Controls and Dimming	
Luminous Flux (Nom)	2375 lm	Dimmable	Yes
Luminous Flux (Rated) (Nom)	2375 lm	Approval and Application	
Color Designation	Warm White (WW)	Energy Efficiency Label (EEL)	A
Correlated Color Temperature (Nom)	3000 K	Mercury (Hg) Content (Nom)	8 mg
Luminous Efficacy (rated) (Nom)	74 lm/W	Energy Consumption kWh/1000 h	35 kWh
Color Rendering Index (Nom)	80	Product Data	
LLMF 2000 h Rated	84 %	Full product code	871150055967800
LLMF 4000 h Rated	79 %		
LLMF 6000 h Rated	75 %		

MASTER TL-E Circular Super 80


Order product name	TL-E 32W/830 1CT/20
EAN/UPC - Product	8711500559678
Order code	928026383074
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20

Material Nr. (12NC)	928026383074
Net Weight (Piece)	0.180 kg
ILCOS Code	FSC-32/30/1B-E-G10q-29/299

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Dimensional drawing




TL-E 32W/830

Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
TL-E 32W/830	30.9 mm	27.1 mm	299.0 mm	303.5 mm	241.0 mm	246.0 mm
1CT/20						

Photometric data



Lightcolor /830



Lightcolor /830

MASTER TL-E Circular Super 80

