



# MASTER TL-E Circular Super 80

## TL-E 32W/865 1CT/20

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes, including decorative ones, in 'human' applications such as schools, offices, shops and homes, and for lighting of residential areas.

### Product data

General Information		LLMF 8000 h Rated	
Cap-Base	G10Q [ G10q]		73 %
Life to 50% Failures (Nom)	13000 h	Operating and Electrical	
LSF 2000 h Rated	98 %	Power (Rated) (Nom)	32.0 W
LSF 4000 h Rated	77 %	Lamp Current (Nom)	0.450 A
LSF 6000 h Rated	60 %	Voltage (Nom)	81 V
LSF 8000 h Rated	45 %	Temperature	
Light Technical		Design Temperature (Nom)	25 °C
Color Code	865 [ CCT of 6500K]	Controls and Dimming	
Luminous Flux (Nom)	2310 lm	Dimmable	Yes
Luminous Flux (Rated) (Nom)	2310 lm	Approval and Application	
Color Designation	Cool Daylight	Energy Efficiency Label (EEL)	A
Correlated Color Temperature (Nom)	6500 K	Mercury (Hg) Content (Nom)	8 mg
Luminous Efficacy (rated) (Nom)	72 lm/W	Energy Consumption kWh/1000 h	35 kWh
Color Rendering Index (Nom)	80	Product Data	
LLMF 2000 h Rated	84 %	Full product code	871150064038300
LLMF 4000 h Rated	79 %		
LLMF 6000 h Rated	75 %		

# MASTER TL-E Circular Super 80


Order product name	TL-E 32W/865 1CT/20
EAN/UPC - Product	8711500640383
Order code	928026386574
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20

Material Nr. (12NC)	928026386574
Net Weight (Piece)	0.110 kg
ILCOS Code	FSC-32/65/1B-E-G10q-29/299

## Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

## Dimensional drawing



TL-E 32W/865

Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
TL-E 32W/865 1CT/20	30.9 mm	27.1 mm	299.0 mm	303.5 mm	241.0 mm	246.0 mm

