



TL-M Rapid Start Standard Colours

TL-M RS 40W/54-765 1SL/25

Low-pressure mercury discharge lamps with a tubular 38 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	54-765
Luminous Flux	2,500 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6200 K
Luminous Efficacy (rated) (Nom)	63 lm/W
Color rendering index (CRI)	72
Operating and Electrical	
Power Consumption	39.5 W
Lamp Current (Nom)	0.430 A
Voltage (Nom)	101 V
Voltage (Nom)	101 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T12 [38 mm (T12)]
Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg
Energy Consumption kWh/1000 h	47 kWh
Product Data	
Order product name	TL-M RS 40W/54-765 1SL/25
Full product name	TL-M RS 40W/54-765 1SL/25
Full product code	871150072441040
Order code	72441040
Material Nr. (12NC)	928030505471
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500724410
Numerator - Packs per outer box	25

TL-M Rapid Start Standard Colours


EAN/UPC - Case	8711500724427
----------------	---------------

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-M RS 40W/54-765 1SL/25	40.5 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

Photometric data



Spectral Power Distribution Colour - TL-M RS 40W/54-765 1SL/25

