



TL-M Rapid Start Super 80

TL-M RS Super 80 65W/840 1SL/25

The TL-M RS (Rapid Start) Super 80 lamp (tube diameter 38 mm) offers more lumens per watt and better color rendering than TL standard colors. The lamp has an external silicon coating and an external ignition strip. It is suitable for situations where low temperatures and high humidity require fast and stable ignition. Rapid Start lamps can be ignited without a starter.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	5,100 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	80 lm/W
Color rendering index (CRI)	85
Operating and Electrical	
Power Consumption	64.0 W
Lamp Current (Nom)	0.670 A


Voltage (Nom)	110 V
Voltage (Nom)	110 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T12
Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg
Energy Consumption kWh/1000 h	74 kWh
Product Data	
Order product name	TL-M RS Super 80 65W/840 1SL/25

TL-M Rapid Start Super 80

Full product name	TL-M RS Super 80 65W/840 1SL/25
Full product code	871150072522640
Order code	928031008471
Material Nr. (12NC)	928031008471
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8711500725226
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500725233

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-M RS Super 80 65W/840 1SL/25	40.5 mm	1,500 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

Photometric data



Spectral Power Distribution Colour - TL-M RS Super 80 65W/840 1SL/25

