



TL10 Plus

T10 PLUS 40W/750 1SL/25

The T10 Plus tubular fluorescent lamp line is available in 20W and 40W and is suitable for new installations, as well as replacement in existing installations. They work in conjunction with electromagnetic ballasts (Conventional and Quick Start) and electronic ballasts. Recommended for all types of installations, they deliver the reliability and guarantee of Philips applications.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	20,000 hour(s)
Light Technical	
Color Code	750 [CCT of 5000K]
Luminous Flux	2,700 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	5000 K
Color rendering index (CRI)	69
Operating and Electrical	
Power Consumption	40 W
Lamp Current (Nom)	0.42 A
Voltage (Nom)	112 V
Voltage (Nom)	112 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T10 [32 mm]
Approval and Application	
Mercury (Hg) Content (Nom)	8.5 mg
Product Data	
Order product name	T10 PLUS 40W/750 1SL/25
Full product name	T10 PLUS 40W/750 1SL/25
Full product code	871869652944700
Order code	928034707502
Material Nr. (12NC)	928034707502
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696529447
Numerator - Packs per outer box	25
EAN/UPC - Case	8718696529454


TL10 Plus

Dimensional drawing



Product
T10 PLUS 40W/750 1SL/25

Photometric data



Spectral Power Distribution Colour - T10 PLUS 40W/750 1SL/25

