



TL-X XL

TL-X XL 20W/33-640 SLV/25

Single-pin low-pressure mercury discharge lamps with a tubular 38 mm envelope

Product data

General Information	
Cap-Base	FA6 [FA6]
Life To 10% Failures (Nom)	21000 h
Life to 50% Failures (Nom)	26000 h
Light Technical	
Colour Code	33-640
Luminous Flux (Nom)	940 lm
Colour Designation	Cool White (CW)
Lumen Maintenance 10000 h (Nom)	0 %
Lumen Maintenance 2000 h (Nom)	88 %
Lumen Maintenance 5000 h (Nom)	83 %
Colour Temperature, horizontal (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	47 lm/W
Colour Rendering Index horiz (Nom)	63
Operating and Electrical	
Power (Rated) (Nom)	20.0 W
Lamp Current (Nom)	0.380 A
Voltage (Nom)	58 V


Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Label	B
Mercury (Hg) Content (Nom)	12.0 mg
Energy Consumption kWh/1000 h	25 kWh
Product Data	
Full product code	871150026135940
Order product name	TL-X XL 20W/33-640 SLV/25
EAN/UPC - Product	8711500261359
Order code	26135940
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	928037703332
Net Weight (Piece)	124.000 g
ILCOS Code	FD-20/41/2B-LC/N-Fa6

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

TL-X XL


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-X XL 20W/33-640 SLV/25	40.5 mm	574 mm	592.5 mm	589 mm	611 mm

TL-X XL 20W/33-640

Photometric data



Lightcolour /33-640



Lightcolour /33-640

