



TL-X XL

TL-X XL 65W/33-640 SLV/25

The TL-X XL lamp (tube diameter 38 mm) has an extended lifetime and is fitted with an internal ignition strip for electromagnetic starterless operation or high-frequency non-preheat operation. In combination with a special lampholder, all possible sparking effects during ignition are eliminated. This lamp is used in flameproof and increased-safety luminaires for both indoor and outdoor applications, such as the (petro-)chemical industry, offshore, mines and any location where traces of explosive gases may be found.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Voltage (Nom)	
Cap-Base	FA6 [FA6]	110 V	
Life to 50% Failures (Nom)	26,000 hour(s)	Voltage (Nom)	
		110 V	
Light Technical		Controls and Dimming	
Color Code	33-640	Dimmable	Yes
Luminous Flux	4,400 lm	Mechanical and Housing	
Color Designation	Cool White (CW)	Bulb Shape	T12 [38 mm (T12)]
Correlated Color Temperature (Nom)	4100 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	69 lm/W	Mercury (Hg) Content (Nom)	12.0 mg
Color rendering index (CRI)	63	Energy Consumption kWh/1000 h	74 kWh
Operating and Electrical		Product Data	
Power Consumption	64.0 W	Order product name	TL-X XL 65W/33-640 SLV/25
Lamp Current (Nom)	0.670 A		

TL-X XL

Full product name	TL-X XL 65W/33-640 SLV/25
Full product code	871150026139740
Order code	928038203332
Material Nr. (12NC)	928038203332
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8711500261397
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500261403

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-X XL 65W/33-640 SLV/25	40.5 mm	1,484.1 mm	1,502.6 mm	1,499.1 mm	1,521.1 mm

Photometric data



Spectral Power Distribution Colour - TL-X XL 65W/33-640 SLV/25

