



TL-D U

TL-D U 18W/840 SLV 24

This fluorescent lamp with a U-shaped tube enables the creation of compact luminaires. Often used for sign lighting and residential lighting, e.g. in post-top lanterns.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Controls and Dimming	
Cap-Base	2G13 [2G13]	Dimmable	Yes
Life to 50% Failures (Nom)	7,500 hour(s)		
Light Technical		Mechanical and Housing	
Color Code	840 [CCT of 4000K]	Bulb Shape	U-T8 [U 26 mm]
Luminous Flux	1,350 lm		
Color Designation	Cool White (CW)	Approval and Application	
Correlated Color Temperature (Nom)	4000 K	Mercury (Hg) Content (Nom)	7 mg
Luminous Efficacy (rated) (Nom)	75 lm/W	Energy Consumption kWh/1000 h	22 kWh
Color rendering index (CRI)	85		
Operating and Electrical		Product Data	
Power Consumption	18 W	Order product name	TL-D U 18W/840 SLV 24
Lamp Current (Nom)	0.370 A	Full product name	TL-D U 18W/840 SLV 24
Voltage (Nom)	60 V	Full product code	872790086004700
Voltage (Nom)	60 V	Order code	928038484002
		Material Nr. (12NC)	928038484002
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8727900860047
		Numerator - Packs per outer box	24

EAN/UPC - Case	8727900860054
----------------	---------------

Dimensional drawing

Product	D (max)	D (min)	A (max)	A (min)	E (min)	E (max)
TL-D U 18W/840 SLV 24	27 mm	23 mm	310 mm	300 mm	90 mm	94 mm

Photometric data



Spectral Power Distribution Colour - TL-D U 18W/840 SLV 24

