



TL-D U

TL-D U 36W/840 SLV/12

This fluorescent lamp with a U-shaped tube enables the creation of compact luminaires. Often used for sign lighting and residential lighting, e.g. in post-top lanterns.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	2G13 [2G13]
Life to 50% failures (nom.)	7500 h
LSF 2000 h Rated	98 %
LSF 4000 h Rated	93 %
LSF 6000 h Rated	72 %
LSF 8000 h Rated	40 %
Light Technical	
Colour Code	841 [CCT of 4100K (841)]
Luminous flux (nom.)	3350 lm
Luminous flux (rated) (nom.)	3350 lm
Colour designation	Cool White (CW)
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	93 lm/W
Colour rendering index (nom.)	85
LLMF 2000 h Rated	85 %
LLMF 4000 h Rated	78 %
LLMF 6000 h Rated	71 %

LLMF 8000 h Rated	65 %
Operating and Electrical	
Power (Rated) (Nom)	36.0 W
Lamp current (nom.)	0.430 A
Voltage (Nom)	110 V
Temperature	
Design temperature (nom.)	25 °C
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	7 mg
Energy consumption kWh/1,000 hours	42 kWh


TL-D U

Product Data

Full product code	871150095468815
Order product name	TL-D U 36W/840 SLV/12
EAN/UPC – product	8711500954688
Order code	95468815
SAP numerator – quantity per pack	1

Numerator – packs per outer box	12
SAP material	928038584002
SAP net weight (piece)	256.000 g
ILCOS code	FDU-36/40/1B-E-2G13


Dimensional drawing




TL-DU 36W/840

Product	D (max)	D (min)	A (max)	A (min)	E (min)	E (max)
TL-D U 36W/840 SLV/12	27 mm	23 mm	607 mm	597 mm	90 mm	94 mm

Photometric data



LDPB_TL-D-U_840-Spectral power distribution B/W



Lightcolour /840

