



TL-D U

TL-D U 36W/840 SLV/12

This fluorescent lamp with a U-shaped tube enables the creation of compact luminaires. Often used for sign lighting and residential lighting, e.g. in post-top lanterns.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	2G13 [2G13]
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	7,500 hour(s)
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	3,250 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	93 lm/W
Color rendering index (CRI)	81
Operating and Electrical	
Power Consumption	37.5 W
Lamp Current (Nom)	0.430 A
Voltage (Nom)	110 V


Voltage (Nom)	110 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	U-T8 [U 26 mm]
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	8 mg
Mercury (Hg) Content (Nom)	7 mg
Energy Consumption kWh/1000 h	38 kWh
EPREL Registration Number	423517
Product Data	
Order product name	TL-D U 36W/840 SLV/12
Full product name	TL-D U 36W/840 SLV/12
Full product code	871150095468815

TL-D U

Order code	95468815
Material Nr. (12NC)	928038584002
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500954688


Numerator - Packs per outer box	12
EAN/UPC - Case	8711500954695

Dimensional drawing



Product	D (max)	D (min)	A (max)	A (min)	E (min)	E (max)
TL-D U 36W/840 SLV/12	27 mm	23 mm	607 mm	597 mm	90 mm	94 mm

Photometric data



Spectral Power Distribution Colour - TL-D U 36W/840 SLV/12

