



# MASTER TL-D 90 De Luxe

## MASTER TL-D 90 De Luxe 58W/930 1SL/10

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


| General Information              |                                 |
|----------------------------------|---------------------------------|
| Cap base                         | G13 [Medium Bi-Pin Fluorescent] |
| Life to 50% failures (nom.)      | 15,000 h                        |
| Light Technical                  |                                 |
| Colour Code                      | 930 [CCT of 3000K]              |
| Luminous Flux                    | 4,350 lm                        |
| Colour designation               | Warm White (WW)                 |
| Chromaticity Coordinate X (Nom)  | 434                             |
| Chromaticity Coordinate Y (Nom)  | 399                             |
| Correlated Colour Temperature    | 3000 K                          |
| Luminous efficacy (rated) (nom.) | 74.4 lm/W                       |
| Colour rendering index (CRI)     | 91                              |
| Operating and Electrical         |                                 |
| Power Consumption                | 58.5 W                          |
| Lamp current (nom.)              | 0.670 A                         |

| Controls and Dimming               |                                       |
|------------------------------------|---------------------------------------|
| Dimmable                           | Yes                                   |
| Mechanical and Housing             |                                       |
| Bulb shape                         | T8 [26 mm (T8)]                       |
| Approval and Application           |                                       |
| Mercury (Hg) content (nom.)        | 2 mg                                  |
| Energy consumption kWh/1,000 hours | 68 kWh                                |
| Product Data                       |                                       |
| Order product name                 | MASTER TL-D 90 De Luxe 58W/930 SLV/10 |
| Full product name                  | MASTER TL-D 90 De Luxe 58W/930 1SL/10 |
| Full EOC                           | 871150088867925                       |
| Order code                         | 88867925                              |
| Material no. (12 NC)               | 928045093081                          |
| Local order code                   | 58930DLP                              |
| SAP numerator – quantity per pack  | 1                                     |
| EAN/UPC – Product/Case             | 8711500888679                         |

MASTER TL-D 90 De Luxe


|                                 |               |
|---------------------------------|---------------|
| Numerator – packs per outer box | 10            |
| EAN/UPC - Case                  | 8711500888686 |

Dimensional drawing




| Product                                  | D (max) | A (max)    | B (max)    | B (min)    | C (max)    |
|------------------------------------------|---------|------------|------------|------------|------------|
| MASTER TL-D 90 De Luxe<br>58W/930 SLV/10 | 28 mm   | 1,500.0 mm | 1,507.1 mm | 1,504.7 mm | 1,514.2 mm |

Photometric data




Spectral Power Distribution Colour - MASTER TL-D 90 De Luxe 58W/930 SLV/10

Lifetime




Life Expectancy Diagram - MASTER TL-D 90 De Luxe 58W/930 SLV/10



Life Expectancy Diagram - MASTER TL-D 90 De Luxe 58W/930 SLV/10

# MASTER TL-D 90 De Luxe

## Lifetime



Lumen Maintenance Diagram - MASTER TL-D 90 De Luxe 58W/930 SLV/10

