



MASTER TL-D 90 De Luxe

MASTER TL-D 90 De Luxe 58W/965 SLV/10

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Power Consumption	59.8 W
Flux measurement reference	Sphere	Lamp Current (Nom)	0.670 A
Life to 50% Failures (Nom)	15,000 hour(s)		
Light Technical		Controls and Dimming	
Color Code	965 [CCT of 6500K]	Dimmable	Yes
Luminous Flux	4,550 lm		
Color Designation	Cool Daylight	Mechanical and Housing	
Chromaticity Coordinate X (Nom)	0.313	Bulb Shape	T8 [26 mm (T8)]
Chromaticity Coordinate Y (Nom)	0.337		
Correlated Color Temperature (Nom)	6500 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	76.1 lm/W	Energy Efficiency Class	G
Color rendering index (CRI)	93	Mercury (Hg) Content (Nom)	1.7 mg
		Energy Consumption kWh/1000 h	60 kWh
		EPREL Registration Number	423531

MASTER TL-D 90 De Luxe

Product Data	
Order product name	MASTER TL-D 90 De Luxe 58W/965 SLV/10
Full product name	MASTER TL-D 90 De Luxe 58W/965 SLV/10
Full product code	871150088873025
Order code	928045096581
Material Nr. (12NC)	928045096581
Local order code	9280-450-96551


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500888730
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500888747

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D 90 De Luxe 58W/965 SLV/10	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL-D 90 De Luxe 58W/965 SLV/10

Lifetime




Life Expectancy Diagram - MASTER TL-D 90 De Luxe 58W/965 SLV/10



Life Expectancy Diagram - MASTER TL-D 90 De Luxe 58W/965 SLV/10

MASTER TL-D 90 De Luxe

Lifetime



Lumen Maintenance Diagram - MASTER TL-D 90 De Luxe 58W/965 SLV/10

