



# TL-D Colored

## TL-D Colored 18W Red 1SL/25

This TL-D lamp (tube diameter 26 mm) helps to create special effects and atmospheres or attract attention by using red, green, blue and yellow light. Apart from using the specific colors, it is also possible to mix the colors to create white light. This lamp offers a high light output, thanks to the use of basic powders. Application areas include shops and showrooms, bars and restaurants, demonstration areas, sign lighting and entertainment stores.

### Product data

General Information	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]
Life To 10% Failures (Nom)	12000 h
Life to 50% Failures (Nom)	15000 h
Light Technical	
Colour Code	150
Luminous Flux (Nom)	25 lm
Luminous Flux (Rated) (Nom)	25 lm
Colour Designation	Red (HO)
Depreciation 2000 hrs	95 %
Operating and Electrical	
Power (Rated) (Nom)	18.0 W
Lamp Current (Nom)	0.360 A
Voltage (Nom)	59 V
Temperature	
Design Temperature (Nom)	25 °C


Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Label	E
Mercury (Hg) Content (Nom)	13.0 mg
Energy Consumption kWh/1000 h	26 kWh
Product Data	
Full product code	871150072684140
Order product name	TL-D Colored 18W Red 1SL/25
EAN/UPC - Product	8711500726841
Order code	72684140
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	928048001505
Net Weight (Piece)	71.000 g

## TL-D Colored

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


### Dimensional drawing




TL-D 18W/150 Red

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D Colored 18W Red	28.0 mm	589.8 mm	596.9 mm	594.5 mm	604.0 mm
1SL/25					

### Photometric data



Lightcolor TL-D /150



Lightcolor TL-D /150

