



# TL-D Colored

## TL-D Colored 18W Green 1SL/25

This TL-D lamp (tube diameter 26 mm) helps to create special effects and atmospheres or attract attention by using red, green, blue and yellow light. Apart from using the specific colors, it is also possible to mix the colors to create white light. This lamp offers a high light output, thanks to the use of basic powders. Application areas include shops and showrooms, bars and restaurants, demonstration areas, sign lighting and entertainment stores.

### Product data

General Information	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]
Life To 10% Failures (Nom)	12000 h
Life to 50% Failures (Nom)	15000 h
Life to 50% Failures Preheat (Nom)	20000 h
Light Technical	
Color Code	170
Luminous Flux (Nom)	1800 lm
Luminous Flux (Rated) (Nom)	1800 lm
Color Designation	Green (G)
LLMF 2000 h Rated	90 %
Operating and Electrical	
Power (Rated) (Nom)	18.0 W
Lamp Current (Nom)	0.360 A
Voltage (Nom)	59 V
Temperature	
Design Temperature (Nom)	25 °C


Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Label (EEL)	A+
Mercury (Hg) Content (Nom)	1.7 mg
Energy Consumption kWh/1000 h	22 kWh
Product Data	
Full product code	871150064298140
Order product name	TL-D Colored 18W Green 1SL/25
EAN/UPC - Product	8711500642981
Order code	928048001705
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	928048001705
Net Weight (Piece)	71.000 g

## TL-D Colored

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


### Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D Colored 18W	28.0 mm	589.8 mm	596.9 mm	594.5 mm	604.0 mm
Green 1SL/25					

TL-D 18W/170 Green

### Photometric data



TL-DCOL 170

