



Blue (/52) TL/TL-D

TL-D 18W/52

Tubular or compact single-ended low-pressure mercury vapour fluorescent lamps

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	13,000 hour(s)
Useful Life (Nom)	2,000 hour(s)
Light Technical	
Color Code	52
Luminous Flux	395 lm
Chromaticity Coordinate X (Nom)	157
Chromaticity Coordinate Y (Nom)	75
Operating and Electrical	
Power Consumption	18 W
Lamp Current (Nom)	0.36 A
Voltage (Nom)	59 V
Voltage (Nom)	59 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T26
Approval and Application	
Mercury (Hg) Content (Nom)	13.0 mg
Product Data	
Order product name	TL-D 18W/52
Full product name	TL-D 18W/52
Full product code	872790083485700
Order code	928048005211
Material Nr. (12NC)	928048005211
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900834857
Numerator - Packs per outer box	25

Blue (/52) TL/TL-D

EAN/UPC - Case	8727900834864
----------------	---------------

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W/52	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

