



TL-D Standard Colours

TL-D 18W/54-765 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Life to 10% failures (nom.)	10000 h
Life to 50% failures (nom.)	13000 h

Light Technical	
Colour Code	54-765
Lamp Luminous Flux 25°C EL (Nom)	1050 lm
Colour Designation	Cool Daylight
Lumen maintenance 10,000 hours (nom.)	75 %
Lumen maintenance 2,000 hours (nom.)	90 %
Lumen maintenance 5,000 hours (nom.)	80 %
Colour Temperature, horizontal (Nom)	6200 K
Colour Rendering Index, horiz (Nom)	72

Operating and Electrical	
Technical Lamp Power (Nom)	18.0 W
Lamp current (nom.)	0.360 A
Voltage (nom.)	59 V

Controls and Dimming	
Dimmable	yes

Approval and Application	
Energy efficiency label (EEL)	B
Mercury (Hg) content (nom.)	8.0 mg
Energy Consumption kWh/1000 h	22 kWh

Product Data	
Full product code	871150070267840
Order product name	TL-D 18W/54-765 1SL/25
EAN/UPC – product	8711500702678
Order code	928048005436
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	928048005436
Net weight (piece)	0.070 kg
ILCOS Code	FD-18/62/2A-E-G13

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

TL-D Standard Colours



Dimensional drawing





TL-D 18W/54-765

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W/54-765 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

Photometric data



Lifetime



TL-D Standard Colours

Lifetime

