



TL-D Blacklight Blue

TL-D 18W BLB 1SL/25

TL-D/08 Blacklight Blue lamps are low-pressure mercury-vapor fluorescent lamps. They have an inner envelope coated with a fluorescent powder that emits long-wave UV radiation to excite luminescence.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Main Application	Blacklight Blue
Life to 50% Failures (Nom)	13000 h
Useful Life (Nom)	5000 h

Light Technical	
Colour Code	108 [08 lead free glass]
Colour Designation	Blacklight Blue
Depreciation 2000 hrs	15 %
Depreciation 5000 hrs	20 %

Operating and Electrical	
Power (Rated) (Nom)	18 W
Lamp Current (Nom)	0.36 A
Voltage (Nom)	59 V

Approval and Application	
Mercury (Hg) Content (Nom)	5.0 mg

UV	
UV-B/UV-A (IEC)	0.2 %
UV-A Radiation 100Hr (IEC)	3.9 W


Product Data	
Full product code	871150095111340
Order product name	TL-D 18W BLB 1SL/25
EAN/UPC - Product	8711500951113
Order code	95111340
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	928048010805
Net Weight (Piece)	71.000 g

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

TL-D Blacklight Blue


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W BLB 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

TL-D 18W/108

Photometric data



Lightcolor /108



Lightcolor /108

