



Actinic BL TL-D(K) Secura

Actinic BL TL-D TL-D 18W/10 Secura 1SL/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL-D(K) Secura lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. In addition, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice.

Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Main application	Reprography (R)
Life to 50% failures (nom.)	13000 h
Useful life (nom.)	9000 h
Light Technical	
Colour code	10
Colour designation	Actinic
Chromaticity coordinate X (nom.)	220
Chromaticity coordinate Y (nom.)	200
Depreciation at 500 Hours	20 %
Depreciation at 500 Hours	30 %
Operating and Electrical	
Power (Rated) (Nom)	18 W
Lamp current (nom.)	0.36 A

Voltage (Nom)	59 V
Approval and Application	
Mercury (Hg) content (nom.)	5.0 mg
UV	
UV-B/UV-A (IEC)	0.2 %
UV-A radiation 100 hours (IEC)	4.5 W
Product Data	
Full product code	872790085383400
Order product name	Actinic BL TL-D TL-D 18W/10 Secura 1SL/25
EAN/UPC – product	8727900853834
Order code	85383400
Local Code	1810SEC
Numerator – quantity per pack	1
Numerator – packs per outer box	25


Actinic BL TL-D(K) Secura

Material no. (12NC)	928048201003
Net weight (piece)	127.500 g

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.



Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D TL-D 18W/10 Secura 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

TL-D 18W/10 SECU

Photometric data



Lightcolour /10

Lightcolour /10

