



Actinic BL TL-D(K) Secura

Actinic BL TL-D TL-D 18W/10 Secura 1SL/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL-D(K) Secura lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. In addition, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice.

Product data


General Information		Voltage (Nom)	
Base	G13 [Medium Bi-Pin Fluorescent]		59 V
Main Application	Reprography (R)	Approval and Application	
Life to 50% Failures (Nom)	13000 h	Mercury (Hg) Content (Nom)	5.0 mg
Useful Life (Nom)	9000 h	UV	
Light Technical		UV-B/UV-A (IEC)	0.2 %
Color Code	10	UV-A Radiation 100Hr (IEC)	4.5 W
Color Designation	Actinic	Product Data	
Chromaticity Coordinate X (Nom)	220	Order product name	Actinic BL TL-D TL-D 18W/10 Secura 1SL/25
Chromaticity Coordinate Y (Nom)	200	EAN/UPC - Product	8727900853834
UV Depreciation at 2000 h	20 %	Order code	258996
UV Depreciation at 5000 h	30 %	Numerator - Quantity Per Pack	1
Operating and Electrical		Numerator - Packs per outer box	25
Power (Rated) (Nom)	18 W	Material Nr. (12NC)	928048201003
Lamp Current (Nom)	0.36 A	Net Weight (Piece)	127.500 g

Actinic BL TL-D(K) Secura

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050



Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D TL-D 18W/10 Secura 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

TL-D 18W/10 SECU

Photometric data



Lightcolor /10

Lightcolor /10

