



# TL-D Standard Colours

## TL-D 36W/29-530 1SL/25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

### Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Controls and Dimming	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	Yes
Light Technical		Mechanical and Housing	
Color Code	29-530	Bulb Shape	T8 [26 mm (T8)]
Luminous Flux	2,975 lumen	Approval and Application	
Color Designation	Warm White (WW)	Mercury (Hg) Content (Nom)	8.0 mg
Correlated Color Temperature (Nom)	2900 K	Product Data	
Color rendering index (CRI)	51	Full product code	694793919442100
Operating and Electrical		Order product name	TL-D 36W/29-530 1SL/25
Power Consumption	36.0 W	Order code	19442100
Lamp Current (Nom)	0.440 A	Numerator - Quantity Per Pack	1
Voltage (Nom)	103 V	Numerator - Packs per outer box	25
Voltage (Nom)	103 V	Material number (12NC)	928048502953
		Full product name	TL-D 36W/29-530 1SL/25
		EAN/UPC - Case	6922341996337


# TL-D Standard Colours

## Dimensional drawing





Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W/29-530 1SL/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

## Photometric data



Spectral Power Distribution Colour - TL-D 36W/29-530 1SL/25

## Lifetime




Life Expectancy Diagram - TL-D 36W/29-530 1SL/25

Life Expectancy Diagram - TL-D 36W/29-530 1SL/25

## TL-D Standard Colours

### Lifetime



Lumen Maintenance Diagram - TL-D 36W/29-530 1SL/25

