



# TL-D Standard Colours

## TL-D 36W/33-640 1SL/25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap base	G13 [ Medium Bi-Pin Fluorescent]
Life to 10% failures (nom.)	10000 h
Life to 50% failures (nom.)	13000 h

Light Technical	
Colour Code	33-640
Luminous flux (nom.)	2850 lm
Colour designation	Cool White (CW)
Lumen maintenance 10,000 hours (nom.)	75 %
Lumen maintenance 2,000 hours (nom.)	90 %
Lumen maintenance 5,000 hours (nom.)	80 %
Correlated Colour Temperature (Nom)	4100 K
Colour rendering index (nom.)	63

Operating and Electrical	
Power (Rated) (Nom)	36.0 W
Lamp current (nom.)	0.440 A

Voltage (Nom)	103 V
---------------	-------

Controls and Dimming	
Dimmable	Yes


Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	8.0 mg
Energy consumption kWh/1,000 hours	43 kWh

Product Data	
Full product code	871150095045140
Order product name	TL-D 36W/33-640 1SL/25
EAN/UPC – product	8711500950451
Order code	95045140
SAP numerator – quantity per pack	1
Numerator – packs per outer box	25
SAP material	928048503312

# TL-D Standard Colours


SAP net weight (piece)	135.000 g
ILCOS code	FD-36/41/2B-E-G13

## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W/33-640 1SL/25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm



## Photometric data



LDPB\_TL-DSTD\_33-640\_0001-Spectral power distribution B/W

Lightcolour /33-640

## Lifetime




LDLE\_TL-DSTD\_0001-Life expectancy diagram

LDLE\_TL-DSTD\_0002-Life expectancy diagram

## TL-D Standard Colours

### Lifetime



LDLM\_TL-DSTD\_0001-Lumen maintenance diagram

