



# TL-D Standard Colours

## TL-D 36W/54-765 1SL/25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

### Product data

General Information	
Base	G13 [ Medium Bi-Pin Fluorescent]
Life To 10% Failures (Nom)	10000 h
Life to 50% Failures (Nom)	13000 h

Light Technical	
Color Code	54-765
Initial lumen (Nom)	2500 lm
Color Designation	Cool Daylight
Lumen Maintenance 2000 h (Nom)	90 %
Lumen Maintenance 5000 h (Nom)	83 %
Correlated Color Temperature (Nom)	6200 K
Color Rendering Index (Nom)	75

Operating and Electrical	
Power (Rated) (Nom)	36.0 W
Lamp Current (Nom)	0.440 A
Voltage (Nom)	103 V

Controls and Dimming	
Dimmable	Yes

Approval and Application	
Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	8.0 mg
Energy Consumption kWh/1000 h	43 kWh


Product Data	
Order product name	TL-D 36W/54-765 1SL/25
EAN/UPC - Product	8711500950475
Order code	251645
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	928048505422
Net Weight (Piece)	135.000 g
ILCOS Code	FD-36/62/2A-E-G13

## TL-D Standard Colours

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050


### Dimensional drawing




TL-D 36W/54-765

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W/54-765	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm
1SL/25					

### Photometric data




Lightcolor /54-765




Lightcolor /54-765

### Lifetime



TL-D Standard Colours Life Expectancy 3 h cycle



TL-D Standard Colours Life Expectancy 12 h cycle

## TL-D Standard Colours

### Lifetime



TL-D Standard Colours Lumen Maintenance 3 h + 12 h cycle

