



TL-D Blacklight Blue

TL-D 36W BLB 1SL/25

TL-D/08 Blacklight Blue lamps are low-pressure mercury-vapor fluorescent lamps. They have an inner envelope coated with a fluorescent powder that emits long-wave UV radiation to excite luminescence.

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


产品数据

一般資訊	
燈座基底	G13 [Medium Bi-Pin Fluorescent]
壽命 (故障率 50%) (標稱)	15,000 h
可用使用始間 (標稱)	12,000 h
照明技術	
色碼	108 [08 lead free glass]
色彩名稱	黑光藍色
運轉與電力	
耗電量	36 W
燈具電流 (標稱)	0.44 A
電壓 (標稱)	103 V
電壓 (標稱)	103 V
機械與外罩	
燈泡形狀	T26 [T 26mm]

認證與應用	
汞 (Hg) 含量 (標稱)	5.0 mg
UV	
UV-A 輻射 100Hr (IEC)	9.5 W
產品資料	
下訂產品名稱	TL-D 36W BLB 1SL/25
完整產品名稱	TL-D 36W BLB 1SL/25
完整產品代碼	871150095115140
訂單代碼	928048510805
材質 Nr. (12NC)	928048510805
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500951151
分子 - 每一外盒包裝	25
EAN/UPC - 箱	8711500951168


TL-D Blacklight Blue

二维绘图



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W BLB 1SL/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

光度数据



Spectral Power Distribution Colour - TL-D 36W BLB 1SL/25

