



TL-D Blacklight Blue

TL-D 36W BLB 1SL/25

TL-D/O8 Blacklight Blue lamps are low-pressure mercury-vapor fluorescent lamps. They have an inner envelope coated with a fluorescent powder that emits long-wave UV radiation to excite luminescence.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Approval and Application	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Mercury (Hg) Content (Nom)	5.0 mg
Light Technical		Product Data	
Color Code	108 [08 lead free glass]	Full product code	871150095115140
Color Designation	Blacklight Blue	Order product name	TL-D 36W BLB 1SL/25
Operating and Electrical		Order code	95115140
Power Consumption	36 W	Numerator - Quantity Per Pack	1
Lamp Current (Nom)	0.44 A	Numerator - Packs per outer box	25
Voltage (Nom)	103 V	Material number (12NC)	928048510805
Voltage (Nom)	103 V	Full product name	TL-D 36W BLB 1SL/25
Mechanical and Housing		EAN/UPC - Case	8711500951168
Bulb Shape	T26 [T 26mm]		

TL-D Blacklight Blue

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W BLB 1SL/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

Photometric data



Spectral Power Distribution Colour - TL-D 36W BLB 1SL/25

