



# TL-D Blacklight Blue

## TL-D 36W BLB 1SL/25

TL-D/08 Blacklight Blue lamps are low-pressure mercury-vapor fluorescent lamps. They have an inner envelope coated with a fluorescent powder that emits long-wave UV radiation to excite luminescence.

### Product data

General Information	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]
Main Application	Blacklight Blue
Life to 50% Failures (Nom)	15000 h
Useful Life (Nom)	12000 h

Light Technical	
Color Code	108 [ 08 lead free glass]
Color Designation	Blacklight Blue
LLMF 2000 h Rated	10 %
LLMF 6000 h Rated	15 %

Operating and Electrical	
Power (Rated) (Nom)	36 W
Lamp Current (Nom)	0.44 A
Voltage (Nom)	103 V

Approval and Application	
Mercury (Hg) Content (Nom)	5.0 mg

UV	
UV-B/UV-A (IEC)	0.2 %
UV-A Radiation 100Hr (IEC)	9.5 W

Product Data	
Full product code	871150095115140
Order product name	TL-D 36W BLB 1SL/25
EAN/UPC - Product	8711500951151
Order code	928048510805
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	928048510805
Net Weight (Piece)	211.000 g

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

# TL-D Blacklight Blue


## Dimensional drawing




TL-D 36W/108

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W BLB 1SL/25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm

## Photometric data



Lightcolor /108



Lightcolor /108

