



TL-D Standard Colours

TL-D 58W/33-640 1SL/25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Life to 10% failures (nom.)	10000 h
Life to 50% failures (nom.)	13000 h

Light Technical	
Colour Code	33-640
Luminous flux (nom.)	4600 lm
Colour designation	Cool White (CW)
Lumen maintenance 10,000 hours (nom.)	75 %
Lumen maintenance 2,000 hours (nom.)	90 %
Lumen maintenance 5,000 hours (nom.)	80 %
Correlated Colour Temperature (Nom)	4100 K
Colour rendering index (nom.)	63

Operating and Electrical	
Power (Rated) (Nom)	58.5 W
Lamp current (nom.)	0.670 A

Voltage (Nom)	111 V
---------------	-------

Controls and Dimming	
Dimmable	Yes


Approval and Application	
Energy efficiency label (EEL)	B
Mercury (Hg) content (nom.)	8.0 mg
Energy consumption kWh/1,000 hours	68 kWh

Product Data	
Full product code	871150095049940
Order product name	TL-D 58W/33-640 1SL/25
EAN/UPC – product	8711500950499
Order code	95049940
SAP numerator – quantity per pack	1
Numerator – packs per outer box	25
SAP material	928049003312

TL-D Standard Colours

SAP net weight (piece)	167.000 g
ILCOS code	FD-58/41/2B-E-G13


Dimensional drawing



TL-D 58W/33-640

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 58W/33-640 1SL/25	28 mm	1500.0 mm	1507.1 mm	1504.7 mm	1514.2 mm



Photometric data



LDPB_TL-DSTD_33-640_0001-Spectral power distribution B/W

Lightcolour /33-640

Lifetime




LDLE_TL-DSTD_0001-Life expectancy diagram

LDLE_TL-DSTD_0002-Life expectancy diagram

TL-D Standard Colours

Lifetime



LDLM_TL-DSTD_0001-Lumen maintenance diagram

