



TL-D Standard Colours

TL-D 58W/33-640 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

| General Information | |
|------------------------------------|---------------------------------|
| Cap-Base | G13 [Medium Bi-Pin Fluorescent] |
| Life to 50% Failures (Nom) | 13,000 hour(s) |
| Light Technical | |
| Color Code | 33-640 |
| Luminous Flux | 4,600 lm |
| Color Designation | Cool White (CW) |
| Correlated Color Temperature (Nom) | 4100 K |
| Color rendering index (CRI) | 63 |
| Operating and Electrical | |
| Power Consumption | 58.5 W |
| Lamp Current (Nom) | 0.670 A |
| Voltage (Nom) | 111 V |


| Voltage (Nom) | 111 V |
|-------------------------------|------------------------|
| Controls and Dimming | |
| Dimmable | Yes |
| Mechanical and Housing | |
| Bulb Shape | T8 |
| Approval and Application | |
| Mercury (Hg) Content (Nom) | 5.0 mg |
| Energy Consumption kWh/1000 h | 68 kWh |
| Product Data | |
| Order product name | TL-D 58W/33-640 1SL/25 |
| Full product name | TL-D 58W/33-640 1SL/25 |
| Full product code | 871150095049940 |

TL-D Standard Colours

| | |
|-------------------------------|---------------|
| Order code | 928049003312 |
| Material Nr. (12NC) | 928049003312 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500950499 |


| | |
|---------------------------------|---------------|
| Numerator - Packs per outer box | 25 |
| EAN/UPC - Case | 8711500950505 |

Dimensional drawing




| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|------------------------|---------|------------|------------|------------|------------|
| TL-D 58W/33-640 1SL/25 | 28 mm | 1,500.0 mm | 1,507.1 mm | 1,504.7 mm | 1,514.2 mm |

Photometric data




Spectral Power Distribution Colour - TL-D 58W/33-640 1SL/25

Lifetime



Life Expectancy Diagram - TL-D 58W/33-640 1SL/25



Life Expectancy Diagram - TL-D 58W/33-640 1SL/25

TL-D Standard Colours

Lifetime



Lumen Maintenance Diagram - TL-D 58W/33-640 1SL/25

