



TL-D Standard Colours

TL-D 58W/54-765 1SL/25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General information	
Base	G13 [Medium Bi-Pin Fluorescent]
Life To 10% Failures (Nom)	10000 h
Life to 50% Failures (Nom)	13000 h

Light technical	
Color Code	54-765
Initial lumen (Nom)	4000 lm
Color Designation	Cool Daylight
Lumen Maintenance 10000 h (Nom)	75 %
Lumen Maintenance 2000 h (Nom)	90 %
Lumen Maintenance 5000 h (Nom)	80 %
Correlated Color Temperature (Nom)	6200 K
Color Rendering Index (Nom)	72

Operating and electrical	
Power (Rated) (Nom)	58.5 W
Lamp Current (Nom)	0.670 A
Voltage (Nom)	111 V

Controls and dimming	
Dimmable	Yes

Mechanical and housing	
Bulb Shape	T8 [26 mm (T8)]


Approval and application	
Mercury (Hg) Content (Nom)	8.0 mg
Energy Consumption kWh/1000 h	68 kWh

TL-D Standard Colours


Product data

Order product name	TL-D 58W/54-765 1SL/25
EAN/UPC - Product	8711500950512
Order code	251686
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	928049005422

Net Weight (Piece)	167.000 g
ILCOS Code	FD-58/62/2A-E-G13




Dimensional drawing



TL-D 58W/54-765 1SL/25

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 58W/54-765 1SL/25	28 mm	1500.0 mm	1507.1 mm	1504.7 mm	1514.2 mm

Photometric data




LDPB_TL-DSTD_54-765-Spectral power distribution B/W

LDPO_TL-DSTD_54-765-Spectral power distribution Colour


TL-D Standard Colours

Lifetime



LDLE_TL-DSTD_0001-Life expectancy diagram

LDLE_TL-DSTD_0002-Life expectancy diagram



LDLM_TL-DSTD_0001-Lumen maintenance diagram

